

PHILIPS

beard trimmer

Beardtrimmer series 3000

1mm precision settings

Stainless steel blades

10h charge/45mins cordless use



QT4000/15



Perfect beard made easy

The most convenient way to start with your beard

Style your beard the way you want with this beard trimmer. Precision from as short as 1mm up to 10mm.

Precision

- 1mm precision
- Easy to select and lock-in length settings, 1-10mm

Skin friendly performance

- Stainless Steel Blades for long-lasting sharpness
- Skin-friendly rounded tips for smooth skin contact

Easy to use

- Up to 45 minutes of cordless use after 10 hours charging
- Ergonomic design for easier handling
- Detachable head for easy cleaning
- 2 year guarantee, worldwide voltage, no oil needed

Highlights

Perfect beard every day



Set the trimmer at the lowest position for a perfect 3-day beard, just 1mm long.

10 lock-in length settings



Turn the wheel to simply select and lock-in the length settings you want from a short beard of 1mm up to a full beard of 10mm, in precise 1mm steps.

Stainless Steel Blades



Get a perfect yet protective trim, time after time. The trimmer's steel blades lightly brush against one another, sharpening themselves as they trim so they stay extra sharp and effective as on day 1.

Skin-friendly high-performance



Blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent irritation.

Cordless Use



Rechargeable only. Up to 45 minutes of cordless power after 10 hours of charging.

Ergonomic design



Easy to hold and use, it's designed to help you trim those hard-to-reach areas.

Easy to clean



Detach the head and rinse it under the tap for easy cleaning. Dry it before you put it back on the appliance.

Built to last



We back this Philips trimmer with a 2-year guarantee: our grooming products are built to last. You'll never need to oil it, and it's compatible with all worldwide voltages.

Specifications

Service

2-year worldwide guarantee

Accessories

Cleaning brush

Create the look you want

Styles: Short beard

Cutting system

Cutter width: 32 mm

Number of length settings: 10

Precision (size of steps): by 1 mm

Comb type: Stubble

Non-scratching teeth: For more comfort

Range of length settings: 1 up to 10 mm

Cutting element: Stainless steel blades

Ease of use

Secured length settings

Zoomring: Easily adjust length settings

Charge indication: On plug

Battery: 1x AAA NiMH

Easy Cleaning: Washable attachments

Power system

Charging time: 10 hours

Running time: Up to 45 minutes

Battery type: Ni-MH

Worldwide voltage: 100–240 V

Design

Handle: Easy grip

