



Philips Avent
Digital Video Baby Monitor

Private & secure (A-FHSS)
2.7 inch color screen
Soothing lullabies & talkback



SCD620

Always close to your baby

Private and secure with A-FHSS technology

The Philips Avent SCD620 enables you to maintain a secure and private connection with your baby at all times. Hear your baby with perfect sound quality and also see your baby in crystal clear vision (2.7" LCD), whether it is day or night.

Private and secure connection

- Private, secure connection with adaptive FHSS technology
- High resolution 2.7" screen with crystal clear night vision
- Hear your baby with clear sound
- Energy saving eco mode with connection indication

Reliability and reassurance

- LED lights show you when your unit is linked and in range

Freedom, flexibility, comforting & soothing

- Range up to 300 meters*
- Excellent operating time for overnight monitoring
- Stay connected with talk back
- Comforting lullabies to calm your little one
- Choose the best sound level for your surroundings



asimpleswitch.com

PHILIPS
AVENT

Highlights

Private, secure & adaptive FHSS



Unique handset pairing for a private, secure connection to your baby. Combined with the new Adaptive FHSS (Frequency Hopping Spread Spectrum) technology for minimal interference.

2.7" color screen



See your baby, day and night, with crystal clear infra-red night vision that automatically switches on in the dark. Enjoy your baby sleeping with the high resolution extra large 2.7" color screen.

Perfect clear sound video

Hear every tiny giggle, gurgle, and hic-up with perfect clarity. Not only see but also hear your baby anytime with high quality, crystal clear sound.

ECO mode



Switch on the ECO mode to reduce power consumption during quiet times in the baby room while still knowing you are connected to your baby via the unique link indication. The ECO mode switches off the audio/video transmissions and the units only connect when the baby makes a sound.

Always connected

Always know when your monitor is in range and connected. The parent unit will alert you when your monitor is out of range or when the power is low, helping you make sure that you are always connected to your baby.

300m Range



Indoor range up to 50 meters*, Outdoor range up to 300 meters*.

Operating time up to 10 hours



The convenient rechargeable parent unit will give you the freedom of cordless monitoring for up to 10 hours before re-charging is required.

Talk back



Sometimes all your baby needs is the soothing sound of your voice. With one click of this essential feature you can connect with your baby from anywhere around the home.



Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Features

- # Languages: English
- Adjustable sound sensitivity
- Adjustable viewing angle
- Android, IOS, Tablet compatible: No
- Audio only mode
- Auto infrared night vision
- Battery and mains operated baby unit: Mains only
- Battery back-up function baby unit: No
- Battery and mains operated parent unit
- Battery operating time parent unit: Superior up to 10 hours
- Belt Clip
- Brightness control
- Comforting night light: No
- Digital Video Technology: Yes, adaptive FHSS
- Digital zoom and pan: No
- Energy saving Eco mode: Eco mode with link indication
- Hand held and rechargeable: Yes, parent unit
- Indoor range up to: 50m
- Outdoor range up to: 300m
- Linked and in range indication
- Low batt/lost connection alert

- Lullabies: Yes, 5x
- Menu Style: Icons
- Mini USB charging
- Private and secure: Yes, adaptive FHSS
- Talkback function
- Temperature sensor: No
- Vibration mode: No
- Video LCD Screen: 2.7" color
- Voice activation screen: Yes, VOX mode

Convenience

- Auto out-of-range warning
- Battery charging indication
- Battery low indication
- Power on indication
- Volume control
- Sensitivity settings
- Wall mountable

Power

- Power supply: 100 – 240V / 50 - 60Hz

Tuner/Reception/Transmission

- Frequency band: 2.4GHz



Issue date 2018-11-08

Version: 8.1.1

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* The operating range of the baby monitor varies depending on the surroundings and factors that cause interference.