

Philips
Earclip Headphones



SHS3701



Mix and Match

Enjoy the bass beat sound of ear-clip headphones that designed for comfort, stability and performance.

Music to your ears

- 27mm speaker driver delivers big sound performance
- Bass beat vents allow air movement for better sound
- Neodymium magnet enhances bass performance and sensitivity

Made to fit you and your lifestyle

- Ear cushions improve wearing comfort and bass response
- Contoured earhook increase wearing comfort and stability
- Asymmetric cable keeps the cable out the way
- 3 sets of interchangeable caps to mix and match any style
- Soft ear pads for ultimate lasting comfort

Always ready to go

- A 1.2m long cable that is ideal for outdoor use

PHILIPS
sense and simplicity

Specifications

Sound

- Acoustic system: open
- Diaphragm: Mylar dome
- Magnet type: Neodymium
- Voice coil: copper
- Frequency response: 12 - 22 000 Hz
- Impedance: 32 ohm
- Maximum power input: 100 mW
- Sensitivity: 102 dB

Connectivity

- Cable Connection: two-parallel, asymmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: copper

Packaging dimensions

- Packaging dimensions (W x H x D): 9.9 x 22 x 3.6 cm
- Nett weight: 0.046 kg

- Gross weight: 0.092 kg
- Tare weight: 0.046 kg
- EAN: 87 12581 33845 9
- Number of products included: 1
- Packaging type: Blister

Outer Carton

- Outer carton (L x W x H): 48.8 x 39.8 x 49.9 cm
- Nett weight: 4.416 kg
- Gross weight: 13.189 kg
- Tare weight: 8.773 kg
- EAN: 87 12581 33847 3
- Number of consumer packagings: 96

Inner Carton

- Inner carton (L x W x H): 23.3 x 23 x 11.3 cm
- Nett weight: 0.276 kg
- Gross weight: 0.732 kg
- Tare weight: 0.456 kg
- EAN: 87 12581 33846 6
- Number of consumer packagings: 6

Highlights

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

27 mm speaker driver

Compact for wearing comfort yet big enough to deliver crisp, powerful sound, the 27 mm speaker driver is a perfect size for non-distorted listening enjoyment.

Bass Beat vents

Bass beat vents allow air movement for better sound with a deep rich bass.

Comfort ear cushions

The special shape and luxurious materials used for the ear cushions ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

Contoured earhook

The earhook stays put behind your ear even when you're on the move, keeping the earphone comfortably in place and sounding great. It is the part contacting the back of your ears and keep the headphones on your ears.

Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.



Issue date 2012-01-20

Version: 3.2.11

12 NC: 8670 000 30437
EAN: 87 12581 33845 9

© 2012 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com