

PHILIPS

Blue car headlight bulb

ColorVision

Type of lamp: H7

Pack of: 2

12 V,55 W



12972CVPBS2



Restyle with light

Add a touch of color

ColorVision adds a touch of color to your car optics in blue, green, yellow or purple. These innovative colored car bulbs are certified road legal, so you can customize your ride while still projecting safe white light.

Color customization for your car

- Color your lights in blue, green, yellow or purple
- Designed for reflector optics for color customization
- Available in most popular automotive lamp types: H4 and H7
- A new coating technology turns light into a touch of color

Designed to see

- React faster with more light
- Colored car lamps that are certified road legal
- Light up the road with 60% more white light

Original Equipment manufacturer

- Philips is the choice of major car manufacturers
- Philips car lamps are made of high-quality quartz glass
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

Highlights

Available in H4 and H7



To find out which Philips ColorVision lamp fits your car, go to www.philips.com/automotive

Color your lights



Philips ColorVision allows to add a personalized touch of color to your car optics. Choose from blue, green, yellow or purple and customize your ride.

Road legal colored car lamps




ColorVision lamps comply with all ECE regulations and come with a certification card to prove they are road legal. Keep it with you in your car at all times.

Designed for reflector optics




Philips ColorVision creates colored effects by reflecting light into the lamp optics. Switch on your headlamps and light up with a touch of color.

React faster with more light




Increased visibility is proven to help you react faster while driving. With 60% more light, ColorVision increases your visibility by 25 meters compared to standard lamps. Anticipate easier to any obstacles that might come your way.

A new coating technology



Thanks to a special coating on the lamps, Philips ColorVision adds a touch of color which is in line with European regulation. So you can customize your ride while still projecting safe white light

60% more white light



Thanks to its technology, Philips ColorVision lights up the road with 60% more white light than any other standard lamp. So you see the road ahead more clearly, while your optics add a touch of color

Car manufacturer choice



For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting

High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

Specifications

Product description

Technology: Halogen

Type: H7

Range: ColorVision

Application: High beam, Low beam

Designation: H7 ColorVision

Homologation ECE

Marking ECE: E1 22Z

Base: PX26d

Electrical characteristics

Voltage: 12 V

Wattage: 55 W

Light characteristics

Lumens: 1500 +/-10% lm

Color temperature: 3350 K

Lifetime

Life time: Up to 400h

Ordering information

Order entry: 12972CVPBS2

Ordering code: 36810928

Packaging Data

EAN3: 8727900368130

EAN1: 8727900368109

Packaging type: S2

Packed product information

Pack Quantity: 2

MOQ (for professionals): 10

Height: 12.8 cm

Width: 4.7 cm

Length: 11 cm

Outerpack information

Gross weight per piece: 0.427 kg

Height: 13.6 cm

Length: 29 cm

Width: 12 cm

Marketing specifications

Expected benefits: Style

Product highlight: Add a touch of colour

