



Philips  
LCD widescreen monitor

61 cm (24") wide

WUXGA

240BW8EB



## Boost your professional productivity

With high resolution, legible text size, a larger viewing area plus convenient built-in speakers, this Philips 240BW8 boots your business productivity - and is ready for immediate or future upgrade to Windows Vista.

### Designed for maximum productivity

- Big, widescreen ideal for viewing two A4 pages side-by-side
- Display more images and content without scrolling
- Tilt, swivel and height-adjust for an ideal viewing position

### Best total cost of ownership solution

- Empowered for Windows Vista
- Complies with RoHS standards to care for the environment

### Outstanding front of screen performance

- WUXGA, wide format 1920x1200 resolution for sharper display
- 5ms fast response time
- DVI-D input and HDCP support

### Great convenience

- Dual input accepts both analog VGA and digital DVI signals
- Embedded power supply eliminates external power adaptors
- Built-in speakers for audio without desktop clutter

**PHILIPS**  
sense and simplicity

LCD widescreen monitor  
61 cm (24") wide WUXGA

240BW8EB/00

# Highlights

## Widescreen

A big, widescreen display that improves productivity by displaying two A4 pages side-by-side.

## Large viewing area

Viewing area is the visible portion of a monitor screen available for displaying data.

## Windows Vista ready

Philips Vista-ready monitors are empowered for vibrant, exciting display of this new, visually sophisticated and demanding Windows operating system, designed to enhance your entertainment experience, make you more productive and help you control your computing experience at home and in the office, making viewing, finding and organizing information for work or play quick, efficient and easy.

## Compliant with RoHS standards

Philips designs and produces display products in compliance with strict Restriction of Hazardous Substances (RoHS) standards that

restrict lead and other toxic substances that can harm the environment.

## WUXGA, wide format 1920 x 1200

Wide format of Ultra Extended Graphics Array, a display specification that is capable of displaying 1920 x 1200 resolution, or approximately 2.3 million pixels.

## 5ms on/off response time

On-Off response time is the period required for a liquid crystal cell to go from active (black) to inactive (white) and back to active (black) again. It is measured in milliseconds. Faster is better: Lower response time means faster transitions and, therefore, results in fewer visible image artifacts in the display of transition of texts and graphics. On-Off response time is a more important measure in the display of business content like documents, graphs and photos.

## HDCP ready

High-Bandwidth Digital Content Protection (HDCP) is a copyright protection system that

is incorporated into the DVI connector. It helps stop unauthorized duplication of copyrighted content. HDCP allows you to play protected content media such as movies and concerts. It checks the signal to prevent piracy, allowing only legal copies of content to display.

## Dual input

Dual input provides connectors to accommodate input of both analog VGA and digital DVI signals.

## Embedded power supply

An embedded power supply is a power adaptor built into the body of a display device that replaces a bulky external power adaptor.

## Built-in speakers

A pair of stereo speakers built into a display device. It can be visible front firing, or invisible down firing, top firing, rear firing, etc depending on model and design.

HDMI x3



HDCP ready



Dual Input



SmartErgoBase



Built-in Speakers



# Specifications

## Picture/Display

- LCD panel type: 1920 x 1200 pixels, Anti-glare polarizer, RGB vertical stripe
- Panel Size: 24" / 61.1 cm
- Effective viewing area: 518.4 mm x 324 mm
- Pixel pitch: 0.270 x 0.270 mm
- Brightness: 250 cd/m<sup>2</sup>
- Contrast ratio (typical): 1000 : 1
- Display colors: 16.7 M
- Viewing angle: 160° (H) / 160° (V), @ C/R > 10
- Response time (typical): 5 ms
- White Chromaticity, 6500K: x = 0.313 / y = 0.329
- White Chromaticity, 9300K: x = 0.283 / y = 0.297
- Maximum Resolution: 1920 x 1200 @ 60Hz (digital input)
- Optimum resolution: 1920 x 1200 @ 60Hz (digital input)
- Video Dot Rate: < 170 MHz
- Horizontal Scanning Frequency: 30 - 83 Hz
- Vertical Scanning Frequency: 56 - 75 Hz
- Aspect ratio: 16:10
- sRGB

## Connectivity

- Signal Input: VGA (Analog), DVI-D, PC Audio in
- Sync Input: Composite Sync, Separate Sync, Sync on Green
- Video input impedance: 75 ohm
- Sync input impedance: 2.2k ohm
- Video input signal levels: 0.7 Vpp

## Convenience

- User convenience: On-screen Display
- Monitor Controls: Input, Auto (Back), Volume control (Down), Brightness (Up), Menu (OK), Power On/Off
- OSD Languages: English, French, German, Italian, Portuguese, Russian, Simplified Chinese, Spanish
- Other convenience: Kensington lock compatible
- Plug & Play Compatibility: DDC/CI, sRGB, Windows 98/ME/2000/XP/Vista
- Regulatory approvals: CE Mark, Energy Star, FCC-B, UL, CSA, SEMKO, TCO '03, TÜV/GS, TÜV

- Ergo, UL/cUL
- Tilt: -3.5° to 21.5°
- Swivel: +/- 45°
- Pivot: 90° (clockwise)
- VESA Mount: 100 x 100 mm
- Built-in Audio: 2 W x 2

## Accessories

- Included accessories: AC Power Cord, VGA cable, Audio Cable
- User Manual

## Dimensions

- Box dimensions (W x H x D): 651 x 560 x 298 mm
- Box dimensions in inch (W x H x D): 25.6 x 22.0 x 11.7 inch
- Set dimensions (W x H x D): 565.6 x 409.8 x 68.3 mm
- Set dimensions in inch (W x H x D): 22.3 x 16.1 x 2.7 inch
- Set dimensions with stand (W x H x D): 565.6 x 445.7 x 220 mm
- Set dimensions with stand in inch (W x H x D): 22.3 x 17.5 x 8.7 inch
- Height adjustment range: 130 mm
- MTBF: 50,000 hrs
- Relative humidity: 20% - 80%
- Temperature range (operation): 5°C to 35°C
- Temperature range (storage): -20°C to 60°C
- Product weight (+stand): 8.8 kg
- Product weight (+stand) (lb): 19.4 lb
- Weight incl. Packaging: 11.9 kg
- Weight incl. Packaging (lb): 26.2

## Power

- Complies with: Energy Star
- Consumption (On mode): < 70 W
- Consumption (Off Mode): < 1 W
- Power LED indicator: Stand by/sleep - Amber, Operation - green
- Power supply: Built-in, 100-240VAC, 50/60Hz



Issue date 2013-01-31

Version: 3.0.3

12 NC: 8670 000 35587  
EAN: 87 12581 38345 9

© 2013 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)