



Philips Evnia Gaming  
Monitor  
4K HDR display with  
Ambiglow

### Designed for Xbox

Evnia 7000  
27" (68.5 cm)  
3840 x 2160 (4K UHD)



279M1RV

## Optimized performance for next-gen console gaming

For true console gaming enthusiasts, the Designed for Xbox display delivers a new era of gaming. Enjoy visual awesomeness and precise color accuracy with UltraClear 4K Nano IPS Display. DisplayHDR 600 gives vibrant image quality.

#### Designed for Xbox

- Designed for Xbox for the optimal gaming experience
- AMD FreeSync™ Premium Pro; smooth, low latency HDR gaming
- SmartImage HDR gives optimal viewing from your HDR content

#### Design to enhance the senses

- Enhanced audio with DTS Sound™
- Ambiglow adds a new dimension to your viewing experience
- 120Hz refresh rates for ultra-smooth, brilliant images
- 144Hz refresh rates for ultra-smooth, brilliant images
- Low input lag reduces time delay between devices to monitor

#### Features for gamers needs

- Certified NVIDIA® G-SYNC® compatible for smooth fast gaming
- IPS Nano color technology extends gamut for vibrant visuals
- Access and display multiple sources on two devices
- LowBlue mode and Flicker-free easy-on-the eyes viewing



reddot winner 2020

EVNIA

PHILIPS

4K HDR display with Ambiglow  
Designed for Xbox Evnia 7000, 27" (68.5 cm), 3840 x 2160 (4K UHD)

279M1RV/00


# Highlights

## Designed for Xbox



Unleash your console gaming. We partnered with the Xbox team to develop this Designed for Xbox display that is validated to deliver the optimal Xbox Series X visual performance the moment you plug it in.

## AMD FreeSync™ Premium Pro



Gaming shouldn't be a choice between choppy gameplay or broken frames. This display is certified with AMD FreeSync™ Premium Pro, which provides a variable refresh rate (VRR) and the true HDR gaming experience. This provides a combination of smooth gaming at peak performance, and exceptional high dynamic range visuals while still maintaining low latency.

## 144Hz Gaming



You play intense, competitive gaming. You demand display with lag free, ultra-smooth

images. This Philips display redraws the screen image up-to 144 times per second, effectively 2.4x faster than a standard display. A lower frame rate can make enemies appear to jump from spot to spot on the screen, making them difficult targets to hit. With 144Hz frame rate, you get those critical missing images on the screen which shows enemy movement in ultra-smooth motion so you can easily target them. With ultra-low input lag and no screen tearing, this Philips display is your perfect gaming partner

## DTS Sound™



DTS Sound is an audio processing solution designed to optimize the playback of music, movies, streaming and games on the PC regardless of form factors. DTS Sound enables an immersive virtual surround sound experience, complete with rich bass and dialog enhancement and maximized volume levels free of any clipping or distortion.

## NVIDIA® G-SYNC® Compatible



When playing intense games with high refresh rates, screen tearing may appear without optimal graphics synchronization. Certified as NVIDIA® G-SYNC® compatible, variable refresh rate (VRR) reducing screen tearing and syncing your monitor's refresh rate with your


graphic card's output for a smoother gaming experience. Scenes appear instantly, objects look sharper, and gameplay is smooth, giving you a stunning visual experience and a serious competitive edge.

## IPS Nano color



For critical imaging, gaming and productivity needs, Nano IPS display provides precise color accuracy across a wide viewing angle without color shift. Richer reds, lush greens, and deeper blues. Ultra Wide-Color with IPS Nano Color technology uses KSF enhanced phosphor nanoparticles to absorb excess light created by the screen to produce amazing color. True-to-life color. Our display panels achieve up to 98% coverage of the DCI-P3 color gamut standard for color purity as defined by The Society of Motion Pictures and Television Engineers for cinematic picture quality.

## MultiView and built-in KVM



Control and switch between two devices through a single keyboard and mouse with the built-in KVM. MultiView lets you survey both sources simultaneously on one screen. With these features, you can reduce cable clutter and save valuable time. Perfect for streamers with two PCs, content creators or when prepping devices for a LAN event.



# Specifications

## Picture/Display

- LCD panel type: Nano IPS
- Backlight type: W-LED system
- Panel Size: 27 inch / 68.5 cm
- Effective viewing area: 603.9 (H) x 347.45 (V) mm
- Aspect ratio: 16:9
- Maximum resolution: HDMI/DP: 3840 x 2160 @ 144 Hz\*; USB-C: 3840 x 2160 @ 120 Hz
- Pixel Density: 163 PPI
- Response time (typical): 1 ms (Gray to Gray)\*
- Low Input Lag
- Brightness: 450 cd/m<sup>2</sup>
- SmartContrast: Mega Infinity DCR
- Contrast ratio (typical): 1000:1
- Pixel pitch: 0.1554 x 0.1554 mm
- Viewing angle: 178° (H) / 178° (V), @ C/R > 10
- Flicker-free
- HDR: DisplayHDR 600 certified
- Color gamut (min.): DCI-P3: 98%\*
- Color gamut (typical): NTSC 112%\*, sRGB 133%\*, Adobe RGB: 110.1%\*
- Picture enhancement: SmartImage game
- Display colors: Color support 1.07 billion colors
- Scanning Frequency: HDMI: 30 - 135 kHz (H) / 48 - 144 Hz (V); DP: 30 - 254 kHz (H) / 48 - 144 Hz (V); USB-C: 30 - 254 kHz (H) / 48 - 120 Hz (V)
- LowBlue Mode
- sRGB
- SmartUniformity: 97 ~ 102%
- Delta E: < 2 (sRGB)
- Ambiglow: 4-sided
- G-SYNC: Compatible 60 Hz ~ 144 Hz (DP)\*
- HDMI 2.1 Feature: VRR, FRL
- AMD FreeSync™ technology: Premium Pro

## Connectivity

- Signal Input: HDMI 2.1 x 3, DP 1.4 x 1, USB-C x 1 (DP Alt mode, PD 65W)
- USB: USB-B x 1 (upstream), USB 3.2 x 4 (downstream with 2 fast charge B.C 1.2)
- Sync Input: Separate Sync
- Audio (In/Out): Headphone out

## Convenience

- Built-in Speakers: 5 W x 2, DTS Sound
- MultiView: PBP (2x devices)
- KVM: USB-C, USB-B
- User convenience: Power On/Off, Menu/OK, Input/Up, Game Settings/Down, SmartImage game/Back
- OSD Languages: Brazil Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Simplified Chinese, Swedish, Turkish, Traditional Chinese, Ukrainian
- Other convenience: Kensington lock, VESA mount

(100x100mm)

- Plug & Play Compatibility: DDC/CI, Mac OS X, sRGB, Windows 10 / 8.1 / 8 / 7

## Stand

- Height adjustment: 130 mm
- Swivel: -/+ 35 degree
- Tilt: -5/20 degree

## Power

- On mode: 62.7 W (typ.)
- Standby mode: 0.5 W (typ.)
- Off mode: 0.3 W (typ.)
- Power LED indicator: Operation - White, Standby mode- White (blinking)
- Power supply: External, 100-240VAC, 50-60Hz

## Dimensions

- Product with stand(max height): 609 x 545 x 282 mm
- Product without stand (mm): 609 x 353 x 75 mm
- Packaging in mm (WxHxD): 730 x 470 x 224 mm

## Weight

- Product with stand (kg): 9.00 kg
- Product without stand (kg): 5.20 kg
- Product with packaging (kg): 12.32 kg

## Operating conditions

- Temperature range (operation): 0°C to 35 °C
- Temperature range (storage): -20°C to 60 °C
- Relative humidity: 20%-80 %
- Altitude: Operation: +12,000ft (3,658m), Non-operation: +40,000ft (12,192m)
- MTBF: 50,000 (Excluded backlight) hour(s)

## Sustainability

- Environmental and energy: RoHS
- Recyclable packaging material: 100 %
- Specific Substances: Mercury free, PVC / BFR free housing

## Compliance and standards

- Regulatory Approvals: CB, TUV/ISO9241-307, TUV-BAUART, CU-EAC, EAEU RoHS, CE Mark

## Cabinet

- Color: Black
- Finish: Textured / Glossy

## What's in the box?

- Monitor with stand
- Cables: DP cable, HDMI cable, USB-C to C cable, Power cable
- User Documentation

Issue date 2023-11-15

© 2023 Koninklijke Philips N.V.  
All Rights reserved.

Version: 7.1.1

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

12 NC: 8670 001 71568  
EAN: 87 12581 77246 8

[www.philips.com](http://www.philips.com)

\* "IPS" word mark / trademark and related patents on technologies belong to their respective owners.  
\* The maximum resolution works for either HDMI input or DP input.  
\* For best output performance, please always ensure that your graphic card is capable of achieving the maximum resolution and refresh rate of this Philips display.  
\* Response time value equal to SmartResponse  
\* BT. 709 / DCI-P3 Coverage based on CIE1976  
\* NTSC Area based on CIE1976  
\* sRGB Area based on CIE1931  
\* Adobe RGB Coverage based on CIE1976  
\* NVIDIA® G-SYNC® support interface: DisplayPort  
\* Make sure to update NVIDIA® G-SYNC® driver to the latest version, see more information on NVIDIA website: <https://www.nvidia.com/>  
\* Make sure your graphic card supports NVIDIA® G-SYNC®  
\* 2020 Advanced Micro Devices, Inc. All rights reserved. AMD, the AMD Arrow logo, AMD FreeSync™ and combinations thereof are trademarks of Advanced Micro Devices, Inc. Other product names used in this publication are for identification purposes only and may be trademarks of their respective companies.  
\* The monitor may look different from feature images.