



Philips Xenon Standard  
Headlight bulb

Type of lamp: D3S

Pack of: 1  
42 V,35 W

42403C1



## Feel safe, drive safe

### Original quality

Philips Xenon Standard is for replacement of the burned-out lamp. It is of the same quality and performance as the original equipped bulb

#### Original quality replacement for your headlight

- Xenon Standard is the original quality replacement option

#### Maximum safety with Xenon HID

- Powerful light from Xenon HID bulb offers maximum safety

#### Original equipment manufacturer

- Adhering to high quality standards of the ECE homologation
- Philips car lamps are made of high-quality quartz glass
- Award-winning car lamp manufacturer
- Philips is the choice of major car manufacturers.
- Philips car lamps are highly resistant against humidity
- Philips car lamps are highly UV resistant

# PHILIPS

Headlight bulb  
Type of lamp: D3S Pack of: 1, 42 V,35 W

# Highlights

## Original quality replacement



Philips Xenon Standard offers the original quality light performance of a new car. The quality of the bulb is endorsed by all major car manufacturers.

## Car manufacturers' choice

For 100 years, Philips has been on the forefront of the automotive lighting industry, introducing technological innovations that have become standard on modern automobiles - Philips is the inventor of Xenon HID technology. Today, one in two cars in Europe and one in three worldwide is equipped with Philips lighting.

## Maximum safety with Xenon HID

Xenon HID (High Intensity Discharge) lamps offer twice as much light\* for safer driving in all conditions. The intense white light produced by the Xenon HID lamps is comparable to daylight. Studies have demonstrated that xenon automotive lighting helps drivers to concentrate on the road and to distinguish obstacles and road signs much faster than traditional lamps. \*compared to standard halogen bulbs

## ECE homologation



Philips Automotive is dedicated to producing best-in-class products and services in the Original Equipment Manufacturer market as well as in after-sales market. Our products are manufactured from high-quality materials and tested to the highest specifications to maximize safety and driving comfort of our customers. Our entire production is meticulously tested, controlled and certified (ISO 9001, ISO 14001 and QSO 9000) to the highest ECE requirements.

## High quality quartz glass



UV-Quartz glass is stronger than hard glass and highly resistant to temperature extremes and vibrations, which eliminates the risk of explosion. Philips quartz-glass lamps (filament 2 650° C and glass 800° C) are able to withstand

42403C1

severe thermal shock. With the capability of increased pressure inside the lamp, UV-quartz glass is able to produce a more powerful light

## Resistance against humidity

Only a burning bulb made of quartz glass (filament 2650°c, glass 800°c) can resist thermal shocks : such as, if a drop of cold water touches the hot bulb, when you drive through water with a broken headlight unit.

## UV Resistant



Philips special anti-UV coating technology protects the headlights against harmful ultraviolet radiation, making Philips UV-coated quartz glass perfect for all driving conditions and ensures their longevity

## Commended Car lamps



Our lamps are often commended by automotive experts.

Headlight bulb  
Type of lamp: D3S Pack of: 1, 42 V,35 W

42403C1

# Specifications

## Product description

- Technology: Xenon
- Application: High beam, Low beam
- Designation: D3S
- Homologation ECE
- Range: Xenon Standard
- Type: D3S
- Base: PK32d-5
- Marking ECE: E4 0A9

## Electrical characteristics

- Wattage: 35 W
- Voltage: 42 V

## Lifetime

- Life time: B3/Tc = 2000/3000

## Light characteristics

- Lumens: 3200 ±450
- Color temperature: 4200

## Marketing specifications

- Expected benefits: Original quality
- Product highlight: Original quality

## Ordering information

- Ordering code: 36765294

## Packaging Data

- Packaging type: C1



Issue date 2020-02-03

Version: 10.0.1

12 NC: 8670 001 19432

© 2020 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* Compared to standard halogen bulbs