



Philips Signage Solutions
D-Line Display

49"

Powered by Android
450cd/m²

SignageSolutions



49BDL4051D

Say more

Smart, fast 24/7 display.

Make it stand out with a faster Philips D-Line Professional display. With Philips superb picture quality and Android SOC more powerful than ever before, capable of delivering complex content to capture your audience's attention. Specificall

Superb picture. Blazing processor speed.

- Android 7. Dedicated Android processor
- Proof of Play for Android content. Know what's playing
- Integrated dual-band WiFi

Effortless setup. Total control.

- Operate, monitor and maintain with CMND & Control
- CMND & Create. Develop and launch your own content
- CMND & Deploy. Install and launch apps remotely
- Integrated mPCIe slot for optional 4G/LTE module

Cost-effective system solution

- FailOver ensures content is always playing
- Integrated HTML5 browser. Play and control online content
- Energy-saving automatic backlight control

PHILIPS

Highlights

Powered by Android

Control your Philips professional display via an internet connection. The integrated Android OS (SoC) lets you install web and native Android apps directly to the display. A built-in scheduler makes it easy to launch apps and content based on time of day, or user.

CMND & Control



Run your display network over a local (LAN) connection. CMND & Control allows you to perform vital functions like controlling inputs and monitoring display status. Whether you're in charge of one screen or 100.

CMND & Create



Take control of your content with CMND & Create. A drag-and-drop interface makes it simple to publish your own content-whether it's a daily specials board or branded corporate information. Preloaded templates and integrated widgets ensure your stills, text, and video will be up and running in no time.


CMND & Deploy

Quickly install and launch any app-even when you're off-site and working remotely. CMND & Deploy lets you add and update your own apps, as well as apps from the Philips Professional Display App Store. Simply scan the QR code, log in to the store, and click on the app you want to install. The app is automatically downloaded and launched.

Integrated mPCIe slot

Easily connect 4G/LTE modules to your Philips professional display. The integrated mPCIe slot enables your display to communicate with other devices that share the same wireless connectivity. Invaluable if you're installing displays in locations such as banks or government buildings, where you cannot get onto the local network.

FailOver



From waiting room to meeting room, never show a blank screen. FailOver lets your Philips Professional Display switch automatically between primary and secondary inputs ensuring content keeps playing even if the primary source goes down. Simply set a list of alternate inputs to be sure your business is always on.

Specifications

Picture/Display

- Diagonal screen size: 48.5 inch / 123.2 cm
- Panel resolution: 1920x1080p
- Optimum resolution: 1920 x 1080 @ 60Hz
- Brightness: 450 cd/m²
- Contrast ratio (typical): 1100:1
- Dynamic contrast ratio: 500,000:1
- Aspect ratio: 16:9
- Response time (typical): 12 ms
- Pixel pitch: 0.55926 x 0.55926 mm
- Display colors: 16.7 million
- Viewing angle (H / V): 178 / 178 degree
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, 3D MA deinterlacing, Progressive scan
- Panel technology: IPS
- Placement: Landscape, Portrait
- Operating system: Android 7.1.2

1152 x 900	66Hz
1280 x 960	60Hz
960x720	75Hz
848 x 480	60Hz
832 x 624	75Hz
800 x 600	56, 60, 72, 75Hz
720 x 400	70Hz
640 x 480	60, 67, 72, 75Hz
640 x 350	70Hz

Video formats

Resolution	Refresh rate
1080p	50, 60Hz
1080i	50, 60Hz
720p	50, 60Hz
576i	50Hz
576p	50Hz
480p	60Hz
480i	60Hz

- MTBF: 50,000 hour(s)
- Humidity range (operation)[RH]: 20 ~ 80% RH (No condensation)
- Humidity range (storage) [RH]: 5 ~ 95% RH (No condensation)

Sound

- Built-in speakers: 2 x 10W RMS

Accessories

- Included accessories: Remote Control, Batteries for remote control, Quick start guide, RS232 cable, AC Power Cord
- Stand: Universal Stand-L (BM05922)(Optional)
- Included Accessories: Edge Alignment Kit (1) - 2pcs, Edge Alignment Kit (2)-1pcs, M2 Screw (x2), M3 screw (x1), Philips logo (x1), RS232 daisy-chain cable, SD card cover (x1), Thumb Screw (x8)

Connectivity

- Video input: Display Port1.2 (x1), DVI-I (x 1), HDMI 2.0 (x2)
- Video output: DisplayPort 1.2 (x1), DVI-I (x1)
- Audio input: 3.5 mm jack
- Audio output: 3.5mm jack
- External control: RJ45, RS232C (in/out) 2.5 mm jack, IR (in/out) 3.5 mm jack
- Other connections: micro USB, USB 3.0, USB 2.0, micro SD, mPCIe

Dimensions

- Set dimensions (W x H x D): 1097.6 x 633.9 x 45.5 mm
- Set dimensions in inch (W x H x D): 43.21 x 24.96 x 1.79 inch
- Bezel width: 9.6 mm (T/L/R), 15.7 mm (B)
- Product weight (lb): 32.63 lb
- Product weight: 14.80 kg
- VESA Mount: 400 x 400 mm, M6

Multimedia Applications

- USB Playback Audio: AAC, M4A, MP3, WMA
- USB Playback Picture: BMP, JPEG, JPG, PNG
- USB Playback Video: MKV, MP4, MPEG, MPG, TS, VOB, WMV, ASF, AVI, DAT, FLV

Supported Display Resolution

Computer formats

Resolution	Refresh rate
1920 x 1200	60Hz
1920 x 1080	60Hz
1680 x 1050	60Hz
1600 x 1200	60Hz
1600 x 900	60Hz
1400 x 1050	60, 75Hz
1440 x 1050	60Hz
1440 x 900	60, 75Hz
1366 x 768	60Hz
1360 x 768	60Hz
1280x1024	60,67,75Hz
1280 x 720	60,70Hz
1280 x 800	60,75Hz
1280 x 768	60Hz, 75Hz
1024x768	60,70Hz
1152 x 864	60, 70, 75Hz

Convenience

- Tiled Matrix: Up to 15 x 15
- Keyboard control: Hidden, Lockable
- Signal loop through: IR Looptthrough, DisplayPort, DVI, RS232
- Network controllable: RJ45, RS232
- Screen saving functions: Pixel Shift
- Picture in picture: PIP

Miscellaneous

- On-Screen Display Languages: English, French, German, Spanish, Polish, Turkish, Russian, Italian, Simplified Chinese, Traditional Chinese, Arabic, Japanese, Danish, Dutch, Finnish, Norwegian, Portuguese, Swedish
- Regulatory approvals: CE, BSMI, CB, EAC, EnergyStar 7.0, FCC, Class A, PSB, UL/cUL, CECP, EPA
- Warranty: 3 year warranty

Power

- Standby power consumption: <0.5 W
- Mains power: AC (100 ~ 240 V) , 2.5A
- Consumption (Typical): 75 W
- Consumption (On mode): 130W (max)
- Energy Label Class: G


Internal Player

- CPU: Dual-Core Cortex-A72 @2GHz, Quad-Core Cortex-A53 @ 1.5GHz, RK3399
- GPU: ARM Mali-T860 MP4
- Memory: 4GB DDR3
- Storage: 16GB EMMC
- Wifi: 2T2R, 802.11 ac/a/b/g/n, WCT07R2201
- Operating system: Android 7.1.2

Operating conditions

- Temperature range (operation): 0 ~ 40 °C
- Temperature range (storage): -20 ~ 60 °C
- Altitude: 0 ~ 3000 m

Philips 49BDL4051D
Version: 1.0
Release Date: 2018/09/17



Issue date 2021-02-28

Version: 4.1.1

12 NC: 8670 001 56731
EAN: 87 12581 75390 0

© 2021 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com