




Philips 6700 series  
4K UHD LED Smart TV  
with Ambilight 3-sided

164 cm (65") Ambilight TV  
1200 Picture Performance Index  
HDR 10+  
Pixel Precise Ultra HD



65PUS6704

## 4K UHD LED Smart TV with Ambilight 3-sided

Bring the emotion into any room with the Philips TV that's designed to fit right in. Picture quality is so sharp you'll think you're there. 4K performance is bright and vibrant. Ambilight sets the mood for movies, music, or gaming.

### Looks great wherever you place it.

- 4K UHD LED TV. Rich color, beautiful detail.
- Ambilight. Take the emotion beyond the screen.
- Slim minimalist frame. Sturdy stand.

### Philips picture precision.

- HDR10+ supported. See more of what the director intended.
- Dolby Vision and Dolby Atmos. Cinematic vision and sound.

### SAPHI. The smart way to enjoy your TV.

- One-button access to a clear icon-based menu.
- Philips TV Collection. Netflix, Prime Video, and more.

### Clear sound. Hear every word.

- Clear audio from full-range speakers.
- Crisp, clear dialogue. Punchy bass.

# PHILIPS

# Highlights

## Ambilight 3-sided




With Philips Ambilight, movies and games feel more immersive. Music gets a light show. And your screen will feel bigger than it is. Intelligent LEDs around the edges of the TV cast on-screen colours onto the walls, and into the room, in real time. You get perfectly tuned ambient lighting. And one more reason to love your TV.

## 4K LED TV

With four times the resolution of conventional Full HD, Ultra HD lights up your screen with over 8 million pixels and our unique Ultra Resolution Upscaling technology. Experience improved images regardless of the original content, and enjoy a sharper picture with superior depth, contrast, natural motion and vivid details.

## Dolby Vision and Dolby Atmos



Support for Dolby's premium sound and video formats means the HDR content you watch will look-and sound-gloriously real. Whether it's the latest streaming series or a Blu-Ray disc set, you'll enjoy contrast, brightness, and color that reflect the director's original intentions. And hear spacious sound with clarity, detail, and depth.


## HDR10+ supported



Your Philips TV is primed to get the most out of the HDR10+ video format. Contrast, color,

and brightness levels are adjusted from frame to frame. Whether it's a must-watch series or the new blockbuster, shadows will be deeper. Bright surfaces will shine. Colors will be truer.

## Saphi Smart TV



SAPHI is a fast, intuitive operating system that makes your Philips Smart TV a real pleasure to use. Enjoy great picture quality and one-button access to a clear icon-based menu. Operate your TV with ease, and quickly navigate to popular Philips Smart TV apps including YouTube, Netflix, and more.



# Specifications

## Ambilight

- Ambilight Version: 3-sided

## Picture/Display

- Display: 4K Ultra HD LED
- Diagonal screen size (metric): 164 cm
- Panel resolution: 3840x2160
- Aspect ratio: 16:9
- Picture enhancement: Micro Dimming, Ultra Resolution, 1200 PPI, Dolby Vision, HDR10+

## Supported Display Resolution

- Computer inputs on all HDMI: up to 4K UHD 3840x2160 @60Hz
- Video inputs on all HDMI: up to 4K UHD 3840x2160 @60Hz, HDR supported, HDR10/HLG (Hybrid Log Gamma), HDR10+/Dolby Vision

## Smart TV Features

- User Interaction: SimplyShare, Wi-Fi Miracast certified\*
- Interactive TV: HbbTV
- Program: Pause TV, USB recording\*
- SmartTV apps\*: Online video stores, Open internet browser, TV on demand, Youtube
- Ease of Installation: Auto detect Philips devices, Network installation wizard, Settings assistant wizard
- Firmware upgradeable: Firmware auto upgrade wizard, Firmware upgradeable via USB, Online firmware upgrade
- Screen Format Adjustments: Advance - Shift, Basic - Fill Screen, Fit to screen, Zoom, stretch, Wide screen
- Philips TV Remote app\*: Apps, Channels, Control, NowOnTV, TV Guide, Video On Demand
- Ease of Use: One-stop smart menu button, Onscreen usermanual

## Processing

- Processing Power: Quad Core

## Tuner/Reception/Transmission

- Digital TV: DVB-T/T2/T2-HD/C/S/S2
- MPEG Support: MPEG2, MPEG4
- Video Playback: NTSC, PAL, SECAM
- TV Program guide\*: 8 day Electronic Program Guide
- Signal strength indication
- Teletext: 1000 page Hypertext
- HEVC support

## Connectivity

- Number of HDMI connections: 3
- Number of USBs: 2
- Number of component in (YPbPr): 1
- Wireless connections: Wi-Fi 802.11n 2x2 integrated, Dual Band
- Other connections: Satellite Connector, Common Interface Plus (CI+), Digital audio out (optical), Ethernet-LAN RJ-45, Audio L/R in, Headphone out
- HDMI features: Audio Return Channel, 4K
- EasyLink (HDMI-CEC): Remote control pass-through, System audio control, System standby, One touch play
- HDCP 2.2: Yes on all HDMI
- Number of CVBS: 1

## Multimedia Applications

- Video Playback Formats: Containers: AVI, MKV, H264/MPEG-4 AVC, MPEG-1, MPEG-2, MPEG-4, WMV9/VC1, HEVC (H.265), VP9
- Subtitles Formats Support: .SML, .SRT, .SUB, .TXT, .ASS
- Music Playback Formats: AAC, MP3, WAV, WMA (v2 up to v9.2), WMA-PRO (v9 and v10)
- Picture Playback Formats: JPEG, BMP, GIF, PNG, 360 photo, HEIF

## Power

- Mains power: AC 220 - 240 V 50/60Hz
- Ambient temperature: 5 °C to 35 °C
- Standby power consumption: <0.3W
- Power Saving Features: Auto switch-off timer, Picture mute (for radio)
- Energy Label Class: A+
- Eu Energy Label power: 100 W
- Annual energy consumption: 146 kW h
- Mercury content: 0 mg
- Presence of lead: Yes\*
- Off mode power consumption: N/A W

## Sound

- Output power (RMS): 20W
- Sound Enhancement: 5 Band Equalizer, A.I. Sound, Clear Dialogue, Dolby Atmos, Dolby Volume Leveler, Night mode, Auto Volume Leveler, Bass Enhancement
- Speaker configuration: 2x10W full range speaker

## Dimensions

- Box dimensions (W x H x D): 1600.0 x 995.0 x 174.0 mm

- Set dimensions (W x H x D): 1461.7 x 851.0 x 88.9 mm
- Set dimensions with stand (W x H x D): 1461.7 x 868.7 x 274.0 mm
- Stand dimensions (W x H x D): 1281.3 x 17.7 x 274.0 mm
- Adjustable stand width (Min.): 806.7 mm
- Adjustable stand width (Max.): 1283.6 mm
- Product weight: 23.9 kg
- Product weight (+stand): 24.3 kg
- Weight incl. Packaging: 32.3 kg
- VESA wall mount compatible: 400 x 200 mm

## Accessories

- Included accessories: Remote Control, 2 x AAA Batteries, Power cord, Quick start guide, Legal and safety brochure, Table top stand


## Color & Finishing

- TV Front: Black High Gloss



## Connections

### Side



### Rear



### Bottom



Issue date 2020-09-04

Version: 11.1.1

12 NC: 8670 001 57655  
EAN: 87 18863 01883 5

© 2020 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* 55 inch, 65 inch, 70 inch, and 75 inch screen sizes boast a stand with adjustable width.

\* EPG and actual visibility (up to 8 days) is country and operator dependent.

\* Energy consumption in kWh per year, based on the power consumption of the television operating 4 hours per day for 365 days. The actual energy consumption will depend on how the television is used.

\* The TV supports DVB reception for 'Free to air' broadcast. Specific DVB operators may not be supported. An up to date list can be found in the FAQ section of the Philips support website. For some operators Conditional Access and subscription are required. Contact your operator for more information.

\* Philips TV Remote app and related functionalities vary per TV model, operator, and country, as well as smart device model and OS. For more details please visit: [www.philips.com/TVRemoteapp](http://www.philips.com/TVRemoteapp).

\* Smart TV app offerings vary per TV model and country. For more details please visit: [www.philips.com/smarty](http://www.philips.com/smarty).

\* USB recording for digital channels only, recordings may be limited by broadcast copy protection (CI+). Country and channel restrictions may apply.

\* Compatibility depends on Wifi Miracast certification & Android 4.2 or later. For more details please refer to your device documentation.

\* This television contains lead only in certain parts or components where no technology alternatives exist in accordance with existing exemption clauses under the RoHS Directive.

\* Actual stand position may look and differ from image shown in the leaflet due to varying screen sizes within the product range. Please refer to the product dimensions in the specification page.