



Philips Signage Solutions  
Multi-Touch Display

65"

Edge-lit LED  
Full HD  
Optical Imaging, 6 Touch points

**Signage**Solutions

**BDL6526QT**

## Discover a new level of interaction

with this multi touch LED display

Get even closer to your audience than ever before. Fast, precise and extremely durable, its high performance is matched by excellent reliability and functionality.

### **Optimised for public viewing**

- Full HD LED for brilliant images with incredible contrast

### **Supreme audience interaction**

- Experience amazing interactivity with true Multi-Touch
- Optical touch technology for advanced user interaction
- True multi-touch with 6 simultaneous touch points
- Compatible with all leading operating systems

### **Innovative solutions for any signage application**

- Optional OPS Insert to create an all-in-one solution

### **Care about you, your business and your audience**

- SmartPower for energy saving

### **Maximising the impact of your message**

- Manage and control your network remotely via SmartControl

# PHILIPS

# Highlights

## Full HD LED technology

Picture Quality matters. Standard displays deliver quality, but you expect more. Imagine crisp detail paired with high brightness, incredible contrast and realistic colours for a true-to-life picture.

## Plug-and-Play Multi-Touch



A brand new level of interactivity is now available thanks to integrated touch technology. More flexibility and optimum simultaneous touch performance coupled with excellent operability opportunities give you the ultimate in user interaction. Multi-Touch displays are equipped with automatic touch recognition. The USB connector is HID-

compliant, providing true plug-and-play operation.

## Optical multi-touch

The sensors on the edge of the screen give you perfect clarity whilst at the same time offering multi-touch interaction, opening up all kinds of possibilities for new interactive applications.

## 6 simultaneous touch points

Enjoy a more interactive experience with up to 6 touch points at the same time. Ideal for when you have more than one user interacting with your application simultaneously, the 6 touch points offer an extremely cost-effective solution.

## Software compatibility

Our touch displays are software-independent and support Windows 8, Windows 7, Vista, XP, Mac OS and Linux.

## OPS Insert

Turn your display into an all-in-one digital signage solution and create a display network that is connected, intelligent and secure. Open

Pluggable Specification (OPS) is an industry-standard slot into which you can add an OPS-standardised media player. This cable-free solution gives you the ability to install, use or maintain your hardware whenever you need to.

## SmartPower



The backlight intensity can be controlled and pre-set by the system to reduce the power consumption by up to 50%, which saves substantially on energy costs.

## SmartControl

SmartControl lets you remotely control and manage your network of displays via RJ45 and RS232C. Easily fine-tune all display settings including resolution, brightness, contrast and cloning of your settings over your complete network.

# Specifications

## Picture/Display

- Diagonal screen size: 64.5 inch / 163.9 cm
- Panel resolution: 1920 x 1080p
- Optimum resolution: 1920 x 1080 @ 60 Hz
- Brightness: 350 cd/m<sup>2</sup>
- Contrast ratio (typical): 5000:1
- Dynamic contrast ratio: 500,000:1
- Surface treatment: Anti-Glare coating
- Aspect ratio: 16:9
- Response time (typical): 8 ms
- Pixel pitch: 0.74 x 0.74 mm
- Display colours: 1.07 Billion
- Viewing Angle (H / V): 178 / 178 degree
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, Progressive scan, 3D MA deinterlacing, Dynamic contrast enhancement

## Interactivity

- Multi-touch technology: Optical sensing
- Touch points: 6 simultaneous touch points
- Plug and play: HID compliant
- Protection glass: 5 mm tempered safety glass

## Connectivity

- Video input: DisplayPort (1.2), HDMI (x 2), DVI-D, VGA (Analogue D-Sub), Component (RCA), Composite (RCA), USB
- Video output: DisplayPort, DVI-I, VGA (Analogue D-Sub)
- Audio input: Audio Left/Right (RCA), 3.5-mm jack
- Audio output: Audio Left/Right (RCA), External speaker connector
- External control: RJ45, IR (in/out) 3.5 mm jack, RS232C (in/out) 2.5 mm jack
- Other connections: USB, OPS

## Supported Display Resolution

### Computer formats

Resolution	Refresh rate
640 x 480	60, 67, 72, 75 Hz
800 x 600	56, 60, 72, 75 Hz
1024 x 768	60 Hz
1280 x 768	60 Hz
1280 x 800	60 Hz
1280 x 1024	60 Hz
1360 x 768	60 Hz
1366 x 768	60 Hz
1440 x 900	60 Hz
1600 x 1200	60 Hz
1920 x 1080	60 Hz
1920 x 1200	60 Hz

### Video formats

Resolution	Refresh rate
480i	60 Hz
480p	60 Hz
576p	50 Hz

576i	50 Hz
720p	50, 60 Hz
1080i	50, 60 Hz
1080p	50, 60 Hz

## Convenience

- Placement: Landscape
- Signal Loop Through: RS232, VGA, IR Loop through
- Network controllable: Card OPS RS232, RS232, RJ45, One Wire (HDMI-CEC)
- Picture performance: Advanced colour control
- Picture in picture: PIP
- Screen-saving functions: Pixel Shift, Low Brightness
- Keyboard control: Hidden, Lockable
- Remote control signal: Lockable
- Energy-saving functions: Smart Power
- Other convenience: Carrying handles
- Ease of installation: Smart Insert

## Dimensions

- Set dimensions (W x H x D): 1488.4 x 863.4 x 78.1 mm
- Product weight: 54.4 kg
- VESA Mount: 400 x 400 mm, M6
- Bezel width: 26.2 mm

## Sound

- Built-in speakers: 2 x 10 W

## Operating conditions

- Temperature range (operation): 5 ~ 40 °C
- Relative humidity: 20 ~ 80 %
- MTBF: 50,000 hour(s)

## Power

- Mains power: 90 ~ 240 VAC, 50/60Hz
- Standby power consumption: <0.5 W

## Accessories

- Included accessories: AC Power Cord, VGA cable, RS232 cable, USB cable, Remote Control, Batteries for remote control, Quick start guide, User manual on CD-ROM
- Optional accessories: HDBaseT OPS Receiver (CRD25)

## Miscellaneous

- On-Screen Display Languages: Arabic, English, French, German, Italian, Japanese, Polish, Spanish, Turkish, Russian, Simplified Chinese, Traditional Chinese
- Regulatory approvals: CE, CCC, FCC, Class B, UL/cUL, RoHS, EPA, CB, C-Tick, EAC, EMF, KUCAS, SASO
- Warranty: 3-year warranty



Issue date 2022-05-16

Version: 1.0.1

12 NC: 8670 001 19772  
EAN: 87 12581 72816 8

© 2022 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)