



Philips Brilliance  
UltraWide LCD Display  
with MultiView

34" / 86.7 cm  
uwQHD (3440 x 1440)

**Brilliance**



**BDM3470UP**

## Wide enough for your best ideas with panoramic UltraWide screen

Expand your experience with this 34" (86 cm) UltraWide Philips display. See the big picture with all the details with this large UltraWide screen. Multitask like never before with multiple applications at once.

### Brilliant performance

- IPS technology for full colors and wide viewing angles
- CrystalClear images with UltraWide QHD 3440 x 1440 pixels
- SmartUniformity for consistent images
- MultiView enables simultaneous dual connect and view

### Designed for people

- Ultra narrow bezel for maximum view and minimum distraction
- SmartErgoBase enables people-friendly ergonomic adjustments
- Low bezel-to-table height for maximum reading comfort
- Built-in stereo speakers for multimedia


### Easy to connect and enjoy

- USB 3.0 enables fast data transfers and smart phone charging
- HDMI-ready for Full HD entertainment

**PHILIPS**

# Highlights

## IPS technology




IPS displays use an advanced technology which gives you extra wide viewing angles of 178/178 degree, making it possible to view the display from almost any angle - even in 90 degree Pivot mode! Unlike standard TN panels, IPS displays gives you remarkably crisp images with vivid colors, making it ideal not only for Photos, movies and web browsing, but also for professional applications which demand color accuracy and consistent brightness at all times.

## UltraWide CrystalClear images



These Philips screens deliver CrystalClear, UltraWide Quad HD 3440 x 1440 pixel images. Utilizing high performance panels with high-density pixel count, 178/178 wide viewing angles, these new displays will make your images and graphics come alive. The UltraWide 21:9 format enables more productivity with more room for side-by-side comparisons and more viewable spreadsheet columns. Whether you are demanding professional requiring extremely detailed information for CAD-CAM solutions, or a financial wizard working on huge spreadsheets, Philips displays delivers CrystalClear images.

## SmartUniformity



Fluctuations in brightness and color on LCD screens are a common phenomenon. Philips SmartUniformity mode delivers accurate images in terms of brightness; which is crucial for photography, design, and printing. With a color metric to assess color accuracy, this mode is calibrated to meet average luminance uniformity is greater than 95%. Selecting this mode will produce uniform and accurate images.

## MultiView technology

With the ultra-high resolution Philips MultiView display you can now experience a world of connectivity. MultiView enables active dual connect and view so that you can work with multiple devices like a PC and notebook simultaneously, for complex multi-tasking.

## Ultra Narrow Bezel



Utilizing latest technology panels, the new Philips displays are designed with minimalistic approach by limiting the outer bezel thickness to about 2.5mm. Combined with in-panel black matrix strip of around 9mm, the overall bezel dimensions are reduced significantly allowing for minimal distractions and maximum viewing size. Especially suited for multi-display or tiling setup like gaming, graphics design and

professional applications, the Ultra narrow bezel display gives you the feeling of using one large display.

## SmartErgoBase



The SmartErgoBase is a monitor base that delivers ergonomic display comfort and provides cable management. The base's people-friendly height, swivel, tilt and rotation angle adjustments position the monitor for maximum comfort that can ease the physical strains of a long workday; cable management reduces cable clutter and keeps the workspace neat and professional.

## Low bezel-to-table height



The Philips monitor, thanks to its advanced SmartErgoBase, can be lowered down almost to desk level for a comfortable viewing angle. Low bezel-to-table height is the perfect solution if you use bifocals, trifocals or progressive lens glasses for your computing work. Additionally, it allows for users with greatly different heights to use the monitor in their preferred angle and height settings, helping them reduce fatigue and strain.

## Built-in stereo speakers

A pair of high quality stereo speakers built into a display device. It can be visible front firing, or invisible down firing, top firing, rear firing, etc depending on model and design.



# Specifications

## Picture/Display

- LCD panel type: IPS technology
- Backlight type: W-LED system
- Panel Size: 34 inch / 86.7 cm
- Effective viewing area: 799.8 (H) x 334.8 (V)
- Aspect ratio: 21:9
- Optimum resolution: 3440 x 1440 @ 60Hz
- Response time (typical): 5 ms (Gray to Gray)\*
- Brightness: 320 cd/m<sup>2</sup>
- Contrast ratio (typical): 1,000:1
- SmartContrast: 40,000,000:1
- Pixel pitch: 0.232 x 0.232 mm
- Viewing angle: 178° (H) / 178° (V), @ C/R > 10
- Picture enhancement: SmartImage
- Display colors: Color support 1.07 billion colors
- Scanning Frequency: 30 - 99 kHz (H) / 23 - 80 Hz (V)
- sRGB

## Connectivity

- USB: USB 2.0 x 2, USB 3.0x2 (1 w/fast charging)\*
- Signal Input: VGA (Analog), DVI-Dual Link (digital, HDCP), DisplayPort x 1, HDMI 2.0 x 1
- Sync Input: Separate Sync, Sync on Green
- Audio (In/Out): PC audio-in, Headphone out

## Convenience

- Built-in Speakers: 3 W x 2
- MultiView: PIP/PBP mode, 2x devices
- User convenience: SmartImage, Multiview, User, Menu, Power On/Off
- Control software: SmartControl
- OSD Languages: Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese, Turkish, Ukrainian, Brazil Portuguese, Czech
- Other convenience: Kensington lock, VESA mount (100x100mm)
- Plug & Play Compatibility: DDC/CI, Mac OS X, sRGB, Windows 10 / 8.1 / 8 / 7

## Stand

- Height adjustment: 180 mm
- Pivot: 90 degree
- Swivel: -170/+170 degree
- Tilt: -5/20 degree

## Power

- ECO mode: 25.9 W (typ.)
- On mode: 29 W (typ.) (EnergyStar 7.0 test

- method)
- Standby mode: < 0.4 W (typ)
- Off mode: Zero watts with AC switch
- Energy Label Class: A
- Power LED indicator: Operation - White, Standby mode- White (blinking)
- Power supply: Built-in, 100-240VAC, 50-60Hz

## Dimensions

- Product with stand(max height): 828 x 627 x 270 mm
- Product without stand (mm): 828 x 378 x 62 mm
- Packaging in mm (WxHxD): 934 x 594 x 224 mm

## Weight

- Product with stand (kg): 9.46 kg
- Product without stand (kg): 6.52 kg
- Product with packaging (kg): 14.27 kg

## Operating conditions

- Temperature range (operation): 0°C to 40°C °C
- Temperature range (storage): -20°C to 60°C °C
- Relative humidity: 20%-80 %
- Altitude: Operation: +12,000ft (3,658m), Non-operation: +40,000ft (12,192m)
- MTBF (demonstrated): 70,000 hrs (excluded backlight)

## Sustainability

- Environmental and energy: EnergyStar 7.0, EPEAT\*, TCO Certified, WEEE, RoHS
- Recyclable packaging material: 100 %
- Post consumer recycled plastic: 65%
- Specific Substances: PVC / BFR free housing, Mercury free, Lead free

## Compliance and standards

- Regulatory Approvals: CE Mark, FCC Class B, SEMKO, cETLus, CU-EAC, CCC, CECP, KC, BSMI

## Cabinet

- Front bezel: Black
- Rear cover: Black
- Foot: Black
- Finish: Texture

## What's in the box?

- Monitor with stand
- Cables: D-Sub cable, DVI-D cable, DP cable, HDMI cable, Audio cable, Power cable
- User Documentation



Issue date 2020-03-11

Version: 11.0.2

12 NC: 8670 001 14589  
EAN: 87 12581 72100 8

© 2020 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* "IPS" word mark / trademark and related patents on technologies belong to their respective owners.  
\* Response time value equal to SmartResponse  
\* EPEAT rating is valid only where Philips registers the product. Please visit <https://www.epeat.net/> for registration status in your country.  
\* The monitor may look different from feature images.