



Philips Brilliance  
4K Ultra HD LCD display

43 (42.51" / 108 cm diag.)  
3840 x 2160 (4K UHD)

**Brilliance**



**BDM4350UC**

## 4K Ultra High Definition

See the big picture with all the details

The expansive 43" class Ultra HD professional Philips display gives you the room to spread out, see the big picture and all the details in 4K Ultra High Definition (four times the resolution of full HD).

### Expand your viewing experience

- Expansive 43-inch class brilliant display
- UltraClear 4K UHD (3840x2160) resolution for precision
- IPS LED wide view technology for image and color accuracy
- MultiView 4K for 4 systems on one screen
- SmartUniformity for consistent images
- SmartImage presets for easy optimized image settings

### Designed for the way you work

- Slim bezel design for a stylish look
- Powerful 7-Watt speakers to unleash your content
- USB 3.0 Hub for convenient access and fast charging
- SmartConnect with DisplayPort, HDMI and VGA connections
- MHL technology for enjoying mobile content on big screen
- VESA mount allows for the perfect setup

**PHILIPS**

4K Ultra HD LCD display  
43 (42.51" / 108 cm diag.) 3840 x 2160 (4K UHD)

BDM4350UC/00


# Highlights

## UltraClear 4K UHD Resolution




These Philips displays utilize high performance panels to deliver UltraClear, 4K UHD (3840 x 2160) resolution images. Whether you are demanding professional requiring extremely detailed images for CAD solutions, using 3D graphics applications or a financial wizard working on huge spreadsheets, Philips displays will make your images and graphics come alive.

## IPS technology



IPS displays use an advanced technology which gives you extra wide viewing angles of 178/178 degree, making it possible to view the display from almost any angle. Unlike standard TN panels, IPS displays gives you remarkably crisp images with vivid colors, making it ideal not only for Photos, movies and web browsing, but also for professional applications which demand color accuracy and consistent brightness at all times.


## MultiView technology for 4K



Philips MultiView feature on this expansive 4K UHD display enables you to have up to four

systems each shown in Full HD on one screen. You can use the Picture-by-Picture (PbP) for monitoring four systems on one screen for control rooms or security. Or for multiple devices like two notebooks side-by-side simultaneously, making collaboration more productive. Or Picture-in-Picture mode (PiP) watching a live football feed from your set-top box, while working on your PC.

## SmartUniformity



Fluctuations in brightness and color on LCD screens are a common phenomenon. Philips SmartUniformity mode delivers accurate images in terms of brightness; which is crucial for photography, design, and printing. With a color metric to assess color accuracy, this mode is calibrated to meet average luminance uniformity is greater than 95%. Selecting this mode will produce uniform and accurate images.

## SmartImage



SmartImage is an exclusive leading edge Philips technology that analyzes the content displayed on your screen and gives you optimized display performance. This user friendly interface allows you to select various modes like Office, Photo, Movie, Game, Economy etc., to fit the application in use. Based on the selection, SmartImage dynamically optimizes the contrast, color saturation and sharpness of images and videos for ultimate display

performance. The Economy mode option offers you major power savings. All in real time with the press of a single button!

## 7-Watt Speakers

A pair of high quality stereo speakers built into a display device. It can be visible front firing, or invisible down firing, top firing, rear firing, etc depending on model and design.

## USB 3.0 Hub with FastCharge

Super Speed USB 3.0 deploys 5.0 gbit/s transfer rate, which is about 10 times faster than USB 2.0 standard significantly reducing data transfer time saving you time and money. With more bandwidth, super speed transfer rates, better power management and superior overall performance, USB 3.0 sets the latest global standard allowing you to use the large capacity storage devices. Now you don't have to wait so long for devices to charge. New FastCharge enables quick charging to charge and go. USB 3.0 is also backward compatible with USB 2.0 devices.

## SmartConnect for 4K

These Philips displays come equipped with the most advanced multi connections like VGA, Display Port, universal HDMI connector, enabling you to enjoy high resolution uncompressed video and audio content. New DisplayPort and HDMI 2.0 connection now enables full 4K resolution at 60Hz for smooth visuals. USB connections ensures that you can have super speed data transfers while having global connectivity. Regardless of what source you use, you can rest assured that this Philips display will ensure your investment is not made obsolete any time soon!



# Specifications

## Picture/Display

- LCD panel type: IPS LCD
- Backlight type: W-LED system
- Panel Size: 42.51 inch (108 cm)
- Effective viewing area: 941.2 (H) x 529.4 (V)
- Display Screen Coating: Anti-Glare, 3H, Haze 1%
- Aspect ratio: 16:9
- Optimum resolution: 3840 x 2160 @ 60Hz
- Response time (typical): 5 ms (Gray to Gray)\*
- Brightness: 300 cd/m<sup>2</sup>
- Contrast ratio (typical): 1200:1
- SmartContrast: 50,000,000:1
- Pixel pitch: 0.2451 x 0.2451mm
- Viewing angle: 178° (H) / 178° (V), @ C/R > 20
- Picture enhancement: SmartImage
- Flicker-free
- Display colors: Color support 1.07 billion colors (10 bits)
- Scanning Frequency: VGA/HDMI: 30 - 99 kHz; DP: 30 - 160 kHz (H) / VGA: 56 - 80 Hz; HDMI/DP: 23 - 80 Hz (V)
- MHL: 1080P @ 60Hz
- sRGB
- Brightness uniformity: 96~105%
- Delta E: <3

## Connectivity

- USB: USB 3.0x4 (1 w/fast charging)\*
- Signal Input: VGA (Analog), DisplayPort x 2, HDMI (2.0) - MHL x 2
- Sync Input: Separate Sync, Sync on Green
- Audio (In/Out): PC audio-in, Headphone out

## Convenience

- Built-in Speakers: 7 W x 2
- MultiView: PIP (2x devices), PBP (4x devices)
- User convenience: SmartImage, Multiview, User, Menu, Power On/Off
- Control software: SmartControl
- OSD Languages: Brazil Portuguese, Czech, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese, Turkish, Ukrainian
- Other convenience: Kensington lock, VESA mount (200x200mm)
- Plug & Play Compatibility: DDC/CI, Mac OS X, sRGB, Windows 10 / 8.1 / 8 / 7

## Power

- ECO mode: 46.5 W (typ.)

- On mode: 63.1 W (typ.) (EnergyStar 6.0 test method)
- Standby mode: <0.5 W (typ.)
- Off mode: Zero watts with AC switch
- Power LED indicator: Operation - White, Standby mode- White (blinking)
- Power supply: Built-in, 100-240VAC, 50-60Hz

## Dimensions

- Product with stand(max height): 968 x 630 x 259 mm
- Product without stand (mm): 968 x 562 x 82 mm
- Packaging in mm (WxHxD): 1070 x 680 x 160 mm

## Weight

- Product with stand (kg): 9.72 kg
- Product without stand (kg): 9.40 kg
- Product with packaging (kg): 14.29 kg

## Operating conditions

- Temperature range (operation): 0°C to 40°C °C
- Temperature range (storage): -20°C to 60°C °C
- Relative humidity: 20%-80 %
- Altitude: Operation: +12,000ft (3,658m), Non-operation: +40,000ft (12,192m)
- MTBF: 70,000 hrs (excluded backlight) hour(s)

## Sustainability

- Environmental and energy: EnergyStar 6.0, RoHS
- Recyclable packaging material: 100 %
- Specific Substances: PVC / BFR free housing, Mercury free

## Compliance and standards

- Regulatory Approvals: CECP, WEEE, KCC, PSE, VCCI, J-MOSS, EPA, BSMI, SEMKO, RCM, CE Mark, FCC Class B, EAC, cETLus, TUV/ISO9241-307, PSB, E-standby, SASO, CB, China RoHS, UKRAINIAN, Kuwait, KUCAS, ICES-003

## Cabinet

- Front bezel: Black
- Rear cover: Black
- Foot: Silver
- Finish: Glossy (Front bezel) / Texture (Foot / Rear cover)

## What's in the box?

- Monitor with stand
- Cables: VGA, HDMI, DP, Audio, Power
- User Documentation



Issue date 2022-06-22

Version: 9.0.1

12 NC: 8670 001 35917  
EAN: 87 12581 73810 5

© 2022 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* This Philips display is MHL certified. However, in case your MHL device does not connect or work correctly, check with your MHL device FAQ or vendor directly for direction. The policy of your device manufacturer may require you to purchase their brand specific MHL cable or adapter in order to work

\* Requires optional MHL certified mobile device and MHL cable. (not included) Please check with your MHL device vendor for compatibility.

\* Standby/Off energy saving of ErP is not applicable for the MHL charging functionality

\* For complete list of MHL-enabled products refer to [www.mhlconsortium.org](http://www.mhlconsortium.org)

\* Fast charging complies with USB BC 1.2 standard

\* Response time value equal to SmartResponse

\* Four inputs required for 4 systems on one screen.