

PHILIPS

Smartphone

S396

Black

LTE(TD/FDD)/TD-SCDMA/WCDMA/GSM

CTS396BK



Selfie time anytime

With 8 MP camera on both sides, Philips S396 lets you take a selfie with more possibilities. From now on, capture anything that touches your heart with you being part of the moment. Breathtaking views. Happy gatherings. All in your hands.

Superb connection

- Excellent surfing experience with TDD-LTE and FDD-LTE

Bright sparks, fast speeds

- Android 5.1
- Dual SIM for 2 groups of contacts

Extras in life

- 8 megapixel front camera for self-portraits and video calls
- Quality shots with 8 megapixel autofocus main camera

Sensational touch

- 5" HD IPS display
- Supreme handing comfort of 63° angled back panel

Highlights


TDD-LTE and FDD-LTE

Your Philips mobile phone incorporates dual 4G mode, that allows you to use mobile internet on a blazing speeds both in TDD-LTE and FDD-LTE networks. Now you can enjoy wider LTE coverage with just one phone.

Android 5.1

Empowered by Android, your Philips mobile phone now comes with a fully customizable mobile platform that is open to a wide range of smart applications and functions. Find your pocket PC, games console and telephone all rolled conveniently into one.

Dual SIM



Organize your life better and keep your contacts separate by using 2 different phone numbers. With Dual SIM, you don't need to carry 2 phones around.

8 megapixel front camera

Bring yourself to the forefront of fun snapshots with the 8 megapixel front camera incorporated into your Philips mobile phone. Besides allowing you to take self-portraits, this front-facing camera feature also means that you can engage in face-to-face communication with video calls with friends or colleagues.

8 megapixel AF main camera

Shoot like a pro on the go with the 8 megapixel autofocus main camera on your Philips mobile phone. Capture life's fleeting moments - big or small - in crystal-clear quality and beam them to friends and family with pride. So you won't miss a memorable shot, night or day.

5" HD IPS display

The IPS technology ensures great viewing from any angle, while the vibrant colors and vivid images render a full-bodied viewing experience. Whether you are showing off your latest snapshots to friends or surfing your favorite websites, the 5" screen gives you an unbeatable visual treat while on the go.

63° superior ergonomic design

Supreme handing comfort of 63° angled back panel, even make it more comfortable to hold in. Wherever you go, you are carrying a signature look and style of extraordinary sensations.

Specifications

Network Features

4G TD-LTE: 1900(B39), 2300(B40), 2600(B38), 2600(B41)

3G: WCDMA, TD-SCDMA

GPRS (Rx+Tx): Class 12, Class B

GSM band: 900, 1800, 1900, 850 MHz

Messaging: Concatenated SMS (Long SMS), E-mail, MMS, Multimedia Message Service, Predefined messages (SMS, MMS), SMS (Short Message Service), SMS multi-target, Predefined SMS

Services: OTA provisioning (WAP, MMS), Internet on mobile, WAP 2.0

Voice Codec: FR/EFR/AMR/HR

EDGE

4G FDD-LTE: 1800(B3), 2100(B1), 2600(B7), 800(B20)

WiFi: IEEE 802.11 b,g,n

Dimensions

Antenna: Integrated

Form Factor: Candy bar

Handset dimensions: 141.9x73x9.65mm

Handset weight: 151g

Handset color: Black

Picture/Display

Main Display Colors: 16.7M

Main Display Resolution: 720X1280 pixel

Main Display Technology: TFT IPS

Diagonal screen size (inch): 5 inch

Capacitive touchscreen

Still Picture Capturing

Camera: Integrated

Flash: built-in

Image sensor type: CMOS

Preview frame rate: 30 frames/second

Picture file format: JPEG

Picture resolution: 8M(3584x2016), Front 8M FF wide-angle

Still Picture Playback

Picture Compression Format: BMP, GIF, GIF (87a & 89a), JPEG

Rotation: 90 degree steps

Slide show

Sound

Ringers: MP3 ringer, Polyphonic (64 tones), AMR ringer

Storage Media

Built-in memory (RAM): 1GB

Memory Card Types: Micro SD

Memory management: Memory status, Dynamic memory allocation

User memory: 5170 MB

Maximum memory card capacity: 64 GB

Built-in memory (ROM): 8GB

Convenience

Buttons and controls: Power On/Off, Side keys

Call Management: Call Forwarding, Call on Hold, Call Time, Call Waiting*, Caller ID*

Conference Call, Emergency Call, Microphone mute, Missed Calls, Multi-party call, Received Calls, Firewall

Clock/Version: Analogue, Digital, International clock

Ease of Use: Graphical User Interface, Hands free mode, Hot Keys, In-flight mode, Vibrate Alert, Dual SIM cards, Dedicated Headset plug

Games and applications: Agenda, Alarm

Clock, Calculator, Calendar, Stopwatch,

Countdown timer, Document Viewer,

Documents Reader, Motion sensor, Widget,

File Manager, Photo Editor

Language available: UI: English, Romanian, Ukrainian, German

Operating System: Android5.1

Personalisation/Customization:

Downloadable Animated GIF, Downloadable

Picture, Downloadable Ringtones, Wallpaper,

Ringtones

Text input: Smart predictive input

Vibrator

Volume control

GPS

Built-in GPS

Supports A-GPS

Connectivity

Modem Capabilities: GPRS, SMS, EDGE, UL 50Mbps, CSFB, DL 150Mbps, HSDPA

42Mbps, HSUPA 11.5Mbps, LTE, TD-SCDMA, WCDMA,

LTE Cat4

PC Link: USB 2.0

Wireless connections: Wi-Fi, Bluetooth

Bluetooth profiles: A2DP, File transfer profile

Bluetooth version: 4.0

Serial connections: USB-MicroUSB data cable

Headset: Via 3.5mm jack connector

Accessories

Standard Package Includes: Battery, Charger, User Manual, USB data cable, Battery charger, Handset, Stereo Headset

OS

Android: Android 5.1

Processor

1.0GHz Quad core processor

Power

Battery Capacity: 2300 mAh(removable)

Battery Type: Lithium-ion

Standby time: 30 days

Talk time: 28hrs



* MicroSD memory card is not included.

* Availability of certain features is subject to valid service subscription from your network operator.

* All visuals provided are for reference purposes only. Actual product features such as phone colors and screenshots may vary from those pictured.

* Specifications indicated are based on an initial full battery charge tested in a laboratory with Bluetooth and WiFi switched off. Actual performance will depend on network service provider and usage.

* Actual available memory for end user usage may vary from market to market due to pre-configuration.

* Specifications indicated are subject to change without prior notice.