

# PHILIPS

WelcomeEye  
intercom panel

WelcomeEye  
Outdoor

Very high image quality

RFID access control

Dual controls

Scalable platform

DES9900VOS



## Greet your guests the best way

With WelcomeEye Outdoor intercom panel

Get equipped with the new Philips WelcomeEye Outdoor intercom panel. It offers remarkable image quality and many functions.

### **Upgradeable solution**

- With its upgradeable platform

### **Neat and modern design**

- With its black and aluminium look

### **Functional and practical**

- With its dual controls
- With its RFID technology
- Protect your installation
- With its monitoring function

### **Very high-quality image**

- With its colour CMOS sensor
- With its night vision
- For a perfect view of your guests

# Highlights

## A high-quality image

Enjoy a new experience with the very high-quality image from the WelcomeEye Outdoor.

## A stylish intercom panel

Take advantage of the WelcomeEye Outdoor intercom panel and its modern look.

## A versatile intercom panel

Open your lock and your gate with the WelcomeEye Outdoor intercom panel.

## Day and night vision

Day and night, welcome your guests in the best way with the WelcomeEye intercom panel.

## Expand your installation

Connect up to three screens, two intercom panels and one camera with the WelcomeEye solution.

## Innovative intercom panel

More security with the RFID technology built in to the Philips intercom.

## The polarity protect function

Secure your installation with the polarity protect function built in to your Philips intercom panel

## View your entrances easily

Monitor your entrances easily with the WelcomeEye Outdoor monitoring function.

## Wide viewing angle

Nothing will escape you with the WelcomeEye intercom panel and its very wide viewing angle (H130° / V90°)

# Specifications

## Electrical features

**Electrical features:** 20V DC / 240mA / 4.8W  
**Electrical connection:** 2 bare wires

## Finish

**Finish:** Grey and black aluminium

## Intercom panel

**Door control:** 12 V/2A max.

**Illuminated call button**

**Installation:** Surface mounted

**Lens:** Not adjustable

**Night vision:** White LEDs (2.5 m)

**RFID:** 125 kHz - 23 badges max.

**Sensor:** C-MOS colour 900TVL

**Viewing angle:** H130°/V90°

**Strike plate control:** 12 V/1.1 A max.  
Labelled

## Kit features

**Dimensions:** 210(h) x 150(l) x 93(d) mm

**Weight:** 0.74kg

## Maximum distance

**Wireless:** 120m

## Operating temperature

**Temperature range:** -20°C / +50°C

## Single product features

**Intercom panel dimensions:** 168 (h) x 82 (l) x 38 (d) mm

**Weight:** 0.33kg

## Use

**Intercom panel:** Outdoor (IP44)

## Warranty

**Years:** 2

## Wiring

**Circuit:** 2-Wire

## Access control

**Options:** Lock and gate

## Standard and certification

**Type:** CE, RoHS, REACH

## Settings

**Ring volume:** Ring volume

