



Philips  
Headphones with mic

40mm drivers/closed-back

On-ear  
Compact folding

FS3MBK



## Rich Bass

Everywhere you go!

The lightweight and compact foldable design makes it the perfect headphones on the go. Enjoy powerful sound with the closed acoustic system. The in-line remote control lets you pick up your phone calls easily.

### Powerful sound

- 40 mm neodymium drivers deliver rich bass and powerful sound

### Always ready to go

- Compact foldable design for easy portability and storage

# PHILIPS

Headphones with mic  
40mm drivers/closed-back On-ear, Compact folding

# Specifications

## Sound

- Acoustic system: Closed
- Magnet type: Neodymium
- Diaphragm: PET
- Frequency response: 8 - 23 000 Hz
- Impedance: 32 Ohm
- Speaker diameter: 40 mm
- Type: Dynamic
- Maximum power input: 40 mW
- Sensitivity: 105 dB

## Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold plated
- Type of cable: OFC
- Microphone: Built-in microphone

FS3MBK/27

# Highlights

## 40mm neodymium drivers

The 40mm drivers are engineered to reproduce a rich bass and powerful sound while on the go.

## Compact foldable design

The compact foldable design allows you to easily fold the headband for perfect foldability and storage.



Issue date 2015-10-13

Version: 1.1.4

12 NC: 8670 001 19677  
UPC: 6 09585 24544 0

© 2015 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)