



Philips Avance Collection  
Food processor

- 1000 W
- Compact 3 in 1 setup
- 3.4 L bowl



HR7778/00

## Maximum variety of recipes, minimum effort

Create home made breads, cakes, drinks and more

This Philips Avance collection Food Processor is the versatile solution for your kitchen needs. With its new innovative metal kneading hook, powerful 1000 W motor and one touch auto button for dough, making bread has never been so easy.

### Baking homemade breads and cakes is now so simple

- Metal kneading hook for perfect bread dough
- Double metal balloon beater for cream and egg whites

### Confidently control power and speed settings

- PowerChop technology for superior chopping performance
- One touch auto buttons for bread dough, whipping and ice

### Easy processing and effortless cleaning

- XXL 18cm discs for faster execution of all ingredients
- Dishwasher safe accessories
- 3.4 L bowl and 2.2 L blender jar for family sized portions

### Carefully selected accessories for best results

- Adjustable disc for slices between 1 – 7 mm
- Additional 4 stainless steel discs included
- Citrus press and 6 glass centrifugal juicer with metal mesh
- Supports wide range of optional accessories

Food processor  
1000 W Compact 3 in 1 setup, 3.4 L bowl

HR7778/00

## Highlights

### Innovative metal kneading hook



Together with the strong motor, this metal kneading hook quickly forms a dough ball from your ingredients. Once the dough is formed, the innovative kneading hook works the dough with the right force and power to enable you to make the tastiest bread.

### Double metal balloon beater



The double metal balloon beater together with the one touch auto button creates fluffy egg whites (up to 600% volume increase) and perfectly whipped cream (up to 200% volume increase). Creating delicious desserts has never been easier!

### One touch auto buttons



In addition to the manual 12 speed + pulse control, this Avance Food Processor comes

with 3 one touch auto buttons. To select them, simply turn the control dial to the "ON" position and press the one touch auto button. The motor then automatically sets the right speed and auto pulse functions for the best results.

### PowerChop technology



## PowerChop

PowerChop technology is a combination of blade shape, cutting angle and inner bowl that provides a superior chopping result in both soft and hard ingredients

### 3.4 L bowl and 2.2 L blender



The XL bowl allows for maximum volumes to be processed in one go, for example up to 7 portions of soup, 7 eggs whites, 1.7 kgs of dough. In addition, the 2.2 L blender easily creates up to 5 smoothie portions in one go.

### XXL Discs for faster execution

Thanks to the XXL discs (18cm), the Philips food processor will provide you a faster performance saving you time and effort while cooking.

### 4 stainless steel discs

This food processor comes with an additional range of 4 stainless steel discs: 1 reversible

shredding disc (fine and coarse) for all types of vegetables, 1 granulating disc for potatoes or cheese, 1 julienne disc for thin vegetable strips and 1 French Fry disc for thick potato strips.

### 6 glass centrifugal juicer



This food processor includes a professional juicing accessory. Thanks to its extra large feeding tube and patented large metal mesh filter, it can juice up to 200% faster compared with other food processor juicers. The patented micromesh filter made of stainless steel squeezes every drop to give you more juice. And thanks to its ergonomic design, it is quicker to clean and store.



[asimpleswitch.com](http://asimpleswitch.com)

### Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Accessories

- Adjustable slicing disc: 1-7 mm
- Spatula
- Juice extractor: 6 glass metal mesh centrifugal juicer
- Blender Jar
- Citrus press
- Double balloon beater
- Metal kneading hook
- Reversible disc: slicing/shredding(coarse/fine)
- Stainless steel S-blade

## Design specifications

- Housing: Stainless steel
- Speed knob: ABS
- Pusher: ABS
- Discs, chopping knife: Stainless steel
- Kneading tool: POM and metal
- Citrus press: PP
- Bowl including lid: SAN
- Knife holder, balloon beater: POM
- S-blade, knife, metal discs: Stainless steel

## General specifications

- Speeds: 12 + pulse

- Cord length: 1 m
- Functions: 30+
- 3 preset buttons
- Integrated cord storage
- Non-slip feet
- Blender jar size: 2.2L
- Blender jar working capacity: 1.5L
- Bowl capacity: 3.4L
- Bowl max working capacity: 2.0L (dry/liquid)
- Bowl max working capacity.: 1000g (Flour)
- RPM-Blender&Grinder Mill(max): Up to 20000 rpm
- RPM-Blender&Grinder Mill(min): Up to 6500 rpm
- RPM-Bowl(max): Up to 1700 rpm
- RPM-Bowl(min): Up to 575 rpm
- Main unit with bowl: 289x254x436 mm

## Technical specifications

- Power: 1000 W
- Voltage: 220-240 V
- Frequency: 50/60 Hz
- Safety: Lid & bowl detection, mechanical 1.5 sec brake



Issue date 2013-05-24

Version: 17.2.1

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* Optional accessories not available in all markets.