



Philips SpeechMike  
Premium  
USB dictation microphone

## Best-in-class recording

with Precision Microphone

The SpeechMike Premium takes dictation to a new level. May it be the free-floating studio quality Precision Microphone, a microphone grille with optimized structure, builtin noise-reduction pop filter or the antimicrobial surface.



LFH3500

### Crafted for comfort

- Ergonomically shaped for perfect fit in the hand
- Freely configurable keys for a personalized workflow
- Integrated motion sensor mutes microphone when not in use
- Optimized control panel for comfortable working

### Designed for detail

- Antimicrobial housing and buttons for hygienic working
- Barcode scanner for streamlined documentation
- Laser-scanned, self-cleaning trackball for smooth operation
- Polished surface for reducing unwanted touch noises

### Tuned for clarity

- Free floating, decoupled microphone for precise recording
- Integrated pop filter for perfect recording quality
- Large speaker area for premium playback
- Metal microphone grille with optimized structure

# PHILIPS

# Highlights

## Antimicrobial housing

The SpeechMike Premium's housing and buttons are made of antimicrobial synthetics, guarding it against all kinds of germs. Antimicrobial materials work against a wide range of different microorganisms such as bacteria (e.g. pneumococcal bacilli and multiresistant microorganisms such as MRSA), viruses (e.g. HIV, influenza, etc.), fungi (e.g. *Aspergillus niger*), or algae. The antimicrobial effect on the SpeechMike Premium lasts for at least five years.

## Barcode scanner

Link client or patient data to a recorded file simply by scanning a bar code (SpeechMike Premium barcode devices only). The scanned information is automatically attached to the dictation file, streamlining the documentation process. All identifying information is entered accurately, increasing security and potential for cost savings. With the SpeechMike Premium, it's possible to scan barcodes from up to 60 cm / 23 inches distance, twice the distance compared to its predecessor.

## Ergonomically shaped

As the rear of a dictation microphone is as important as the front, Philips put an emphasis on shaping it in a way so that it perfectly fits the human hand and reduces unintentional use of buttons. The trigger and the "command" button on the rear housing are engineered to be exactly where they need to be. There has never been a desktop dictation device that is as ergonomic as the SpeechMike Premium.

## Free-floating microphone

The microphone in the new SpeechMike Premium is decoupled from its housing for the most incredible crystal clear recording performance ever to be delivered by a desktop dictation device. The completely redesigned microphone suspension guarantees that almost no background, touch, click, air or structure-borne noise is recorded. This technique is derived from studio microphones to make sure there are no sound distortions whatsoever – and to guarantee outstanding speech recognition results.

## Freely configurable keys

With four freely configurable function buttons placed at the lower area of the control panel, the SpeechMike Premium can be further personalized for any user and application. Work the way you want – a benefit that only a Philips SpeechMike offers.

## Integrated motion sensor

Being on the cutting edge of technology, the Philips SpeechMike Premium comes with an integrated motion sensor, making it the first stationary dictation device that can be controlled by the movement of your hand. It detects when it's put on the table, mutes the microphone, and once it is being picked up again it unmutes the microphone. There are plenty

of situations this feature can be greatly beneficial; just think of an incoming phone call or someone stepping in your office. In addition to that, custom events can be programmed, e.g., to pause and to continue the recording.

## Integrated pop filter

The microphone area of the SpeechMike Premium is made of many different layers to make it sound as clear and original as possible. One of those is a fleece inserted above and below the microphone capsule. The fleece filters out sound distortions such as pop and hiss noise, guaranteeing perfect results even if dictating closely into the microphone.

## Larger speaker area

Compared to its predecessor, the SpeechMike Premium is equipped with a double sized-speaker area that enables it to play back recordings in clear and crisp quality.

## Laser-scanned steel trackball

The SpeechMike Premium includes a built-in highprecision stainless steel trackball. Self lubricated and abrasive resistant Teflon bearings guarantee a smooth operation over the entire lifetime. In combination with a laser scanner and self-cleaning features, the trackball is as precise and durable as never before. On top of that, the trackball can even be taken out of the device for cleaning, if this should ever be required.

## Metal microphone grille

A well-engineered microphone grille is able to make a high-end microphone as in the new SpeechMike Premium stand out even more. The hexagonal holes used for the metal grille feature three times more open surface than its predecessor, engineered to provide crystal clear recordings.

## Optimized control panel

Philips is the creator of the ergonomic zones design. SpeechMike Premium has been tested and proven by users to have the most comfortable fit in the human hand. The dictation zone is optimized to keep thumb movement to a minimum. The buttons needed for the actual dictation functions are placed centrally, in the area most convenient for the thumb, guaranteeing perfect ergonomics and nonfatiguing usage for the user. Less frequently needed function buttons are clearly arranged above and below. All buttons used are formed to give as much tactile feedback as possible.

## Polished surface

The housing of the SpeechMike Premium is made of high-class polymers. It is endued with a polished surface and the material includes a pearl metal additive providing a high quality metallic effect and making it non-sensitive to touch noises and fingerprints.

# Specifications

## Connectivity

- USB: High-speed USB 2.0

## Dimensions

- Product dimensions (WxDxH): 45 x 175 x 32 mm
- Product weight (g): 200 - 210 g
- Cable length: 250 cm

## System Requirements

- DVD-ROM drive
- Hard disk space: 250 MB / 30 MB
- Operating System: Windows 8/7/Vista, Mac OS
- Processor: Intel Pentium 4, 1.0 GHz
- RAM memory: 1 GB (2 GB recommended)
- USB: Free USB port
- Compatible with: Citrix, Windows Terminal S.
- Video card: DirectX-compliant graphics

## Audio recording

- Characteristic: uni-directional
- Frequency response: 200 – 12 000 Hz
- Microphone capsule: 10 mm
- Microphone type: electret condenser microphone
- Sensitivity: -37 dBV
- Signal-to-noise ratio: > 70 dBA

## Barcode scanner (LFH3600/3610)

- Compatible bar codes: EAN, UPC, Codabar, MSI, etc
- Laser class: class 1 laser product

## Design and finishing

- Color(s): Dark grey pearl metallic
- Materials: antimicrobial housing

## Green specifications

- Compliant to 2002/95/EC (RoHS): 2002/95/EC (RoHS)
- Lead-free soldered product

## Operating conditions

- Temperature: 5° – 45° C / 41° – 113° F

## Package contents

- CD-ROM with software
- Microphone holder
- Quick start guide
- SpeechMike Premium
- USB cable (linked with device)

## Sound

- Acoustic frequency response: 300 – 7500 Hz
- Speaker diameter: 30 mm
- Speaker output power: 200 mW
- Speaker type: built-in round dynamic speaker



Issue date 2014-03-14

Version: 2.1.1

12 NC: 8670 001 13923  
UPC: 6 09585 24258 6

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)